

**SEL-2725**

5-Port Ethernet Switch  
 Unmanaged  
 Copper Ports 10/100 Mbps  
 Fiber Port 100 Mbps

Part Number:

2	7	2	5					X	
---	---	---	---	--	--	--	--	---	--

**Port Configuration**

One Fiber-Optic Port, Four Copper Ports					S				
Two Fiber-Optic Ports, Three Copper Ports*					D				

**Power Supply**

12 Vdc					D	3			
24/48 Vdc						0			
125/250 Vdc or Vac						2			

**Fiber Interface**

100BASE-FX (1300 nm Multimode LC Connector, 2 km)							2		
100BASE-LX10 (1310 nm Single-Mode LC Connector, 15 km)*							3		

**Conformal Coat**

None									0
Conformally Coated Circuit Boards*									1

**Accessories**

SEL-CA605 CAT5E, Shielded Twisted Pair (STP) Cable*	Please see Online MOT or contact SEL REP or CSR for ordering information.									
SEL-C808 Multimode Fiber-Optic Cable*	Please see Online MOT or contact SEL REP or CSR for ordering information.									
SEL-C809 Single-Mode Fiber-Optic Patchcord*	Please see Online MOT or contact SEL REP or CSR for ordering information.									
15 Vdc Output, 100-240 Vac, 50-60 Hz Input*	2	4	0	-	0	0	5	6		
International Plug Adapter Kit (UK, EU, AUS) for 240-0056*	2	4	0	-	0	0	5	5		
<b>Mounting Accessories</b>										
	DIN Rail Mounting Kit*	9	1	5	9	0	0	1	5	
	Dual Door 651R Mounting Kit <sup>(1)*</sup>	9	1	5	9	0	0	1	7	4
	Single Door 651R Mounting Kit <sup>(1)*</sup>	9	1	5	9	0	0	1	7	5

\* Additional Cost

<sup>(1)</sup> SEL-2725 must be equipped with the 12 Vdc power supply for use with the SEL-651R Advanced Recloser Control.

*Making Electric Power Safer, More Reliable, and More Economical®*

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990