

## SEL-C805 Multimode Fiber-Optic Cable

200 Micron Core Diameter, Hard-Clad Silica Fiber-Optic Cable<sup>(1)</sup>

Part Number:

C	8	0	5					0											
---	---	---	---	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--

### Cable Construction

Zipcord 1 Fiber*					Z	0	1												
Zipcord 2 Fibers*					Z	0	2												
Heavy Duty PVC Jacketed 2 Fibers*					D	0	2												
Heavy Duty PVC Jacketed 4 Fibers*					D	0	4												
Waterproof Heavy Duty Jacketed 2 Fibers*					G	0	2												
Waterproof Heavy Duty Jacketed 4 Fibers*					G	0	4												

### Jacket Marking

Standard								0											
----------	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--

### Termination

Bulk Cable: No Terminations								0	0										
V-Pin Connectors on Both Ends								V	V										
ST <sup>®</sup> Connector on Both Ends								S	S										

### Other Options

No Options																		X	
Pulling Loop (For use with Heavy Duty cables only)*																		1	

### Length

Specify length Enter length in meters with leading zeros. (Example: 15 meters = 0015)																			
--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

### Accessories

Termination Kits	
V-Pin Termination Kit*	T 8 0 0
ST Connector Termination Kit*	2 4 0 - 1 5 0 1
Fiber Stripper - Replacement Blade Kit*	9 1 5 9 0 0 2 5 2
Connectors	
V-Pin Connector*	P 8 0 0
V-Pin Connectors (Pack of 25) *	9 1 5 9 0 0 0 6 7
ST Connector*	0 9 0 - 5 0 0 1
Splice Bushings	
V-Pin Connector Splice Bushing*	S 8 0 0
ST Connector Splice Bushing*	0 9 0 - 5 0 1 2
V-Pin Latch Kit (Pack of 10)*	9 2 1 0
Magnetic Cable Guide*	M C G

\* Additional Cost

<sup>(1)</sup> Cables are priced per options selected.

*Making Electric Power Safer, More Reliable, and More Economical*®

---

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990