

SEL-3400 IRIG-B Distribution Module⁽¹⁾

Part Number:

3 4 0 0 A 1 0 0 D

Firmware

Standard

A

Mounting

Horizontal Rack Mount

1

IRIG-B Input Ports

Two BNC IRIG-B000, B002, B004 Compatible Demodulated Inputs

0

IRIG-B Output Ports

Twelve Demodulated IRIG-B BNC Outputs

0

Display

12/24 Hour LED Time Display

D

Conformal Coat

None

X

Conformal Coated Circuit Boards*

1

Accessories

Time-Distribution Accessories

RG-58 Cable, BNC Connectors on Both Ends	C 9 5 3
BNC terminator, 50 ohm*	2 4 0 - 1 8 0 0
BNC Tee (Female/Female/Male, Equipment Mount)*	2 4 0 - 1 8 0 1
BNC Tee (Female/Male/Female, Equipment Mount)*	2 4 0 - 1 7 9 9
BNC Tee (Female/Female/Female, In-Line Cable)*	2 4 0 - 1 8 0 2
RG-58 Cable, BNC Connector to Tinned Wires	C 9 6 2
RG-58 Cable, Tinned Leads at Both Ends	C 9 6 3
Wire-lead terminator, 50 ohm*	9 1 5 9 0 0 0 3 6

* Additional Cost

⁽¹⁾ Power Supply Input Range: 18-300 Vdc and 85-264 Vac (50-60 Hz)

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990