

SEL-2516

Remote I/O Module

Part Number:

2	5	1	6	0					1	X
---	---	---	---	---	--	--	--	--	---	---

Mounting

Horizontal Rack Mount									0					
-----------------------	--	--	--	--	--	--	--	--	---	--	--	--	--	--

Power Supply

48/125 Vdc or 125 Vac										3				
-----------------------	--	--	--	--	--	--	--	--	--	---	--	--	--	--

125/250 Vdc or Vac										4				
--------------------	--	--	--	--	--	--	--	--	--	---	--	--	--	--

Fiber-Optic Interface

SEL-2800 Compatible (V-pin connector, 200 µm core multimode fiber, 650 nm, 500 m range)										1				
---	--	--	--	--	--	--	--	--	--	---	--	--	--	--

SEL-2815 Compatible (ST connector, 62.5 or 50 µm core multimode fiber, 820 nm, 15 km range) ^{†*}										2				
---	--	--	--	--	--	--	--	--	--	---	--	--	--	--

SEL-2830 Compatible (ST connector, 9 or 10 µm core single-mode fiber, 1300 nm, 80 km range) ^{†*}										3				
---	--	--	--	--	--	--	--	--	--	---	--	--	--	--

SEL-2829 Compatible (ST connector, 9 or 10 µm core single-mode fiber, 1300 nm, 23 km range) [*]										4				
--	--	--	--	--	--	--	--	--	--	---	--	--	--	--

I/O Board Configuration

I/O Board with 8 Standard Outputs, 8 Inputs														1		
---	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--

Control Input Voltage

24 Vdc															1	
--------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

48 Vdc															2	
--------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

110 Vdc															3	
---------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

125 Vdc															4	
---------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

220 Vdc															5	
---------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

250 Vdc															6	
---------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

Accessories

Literature																
	Printed Instruction Manual ⁽¹⁾															

* Additional Cost

⁽¹⁾The SEL-2516 comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each purchased.


[†] Includes one 91560 attenuator for use on links less than 2 km (SEL-2815 compatible) or 16 km (SEL-2830 compatible).

Note: Order part number 9260018 for additional SEL-2516 label kits.

Complete Your Order

The SEL-2516 Remote I/O Module uses SEL Fast Messages over a fiber-optic link to provide device contact I/O for SEL Communications Processors. To complete your order, select the additional components outlined in the alternatives below.

To connect one end of the fiber-optic cable to an SEL-2516 Module and the other end to an SEL Communications Processor.



500 Meters or Less	15 Kilometers or Less	23 Kilometers or Less	80 Kilometers or Less
SEL-2800M1	SEL-2815M	SEL-2829M	SEL-2830M
V-Pin	ST	ST	ST
SEL-C805 Multimode Fiber-Optic Cable (WI-4092)	- SEL-C805 Multimode Fiber-Optic Cable (WI-4092) - SEL-C807 Multimode Fiber-Optic Patchcord (WI-4132)	- SEL-C809 Single-mode Fiber-Optic Patchcord (WI-4133)	- SEL-C809 Single-mode Fiber-Optic Patchcord (WI-4133)

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990