

Installed SFPs (Slots 1-4)

None															A				
4 1000BASE-SX SFP, 550 m, Multimode, LC, 8131-01*															B				
4 1000BASE-LX SFP, 10 km, Single-Mode, LC, 8130-01*															C				
4 10/100/1000BASE-T SFP, 100 m, RJ45, 8115-01*															D				

Conformal Coat

None																				0
Conformally Coated Circuit Boards*																				1

Accessories

Literature		
	Instruction Manual for SEL-2730M	P M 2 7 3 0 M - 0 1
Mounting Bezel		
	Small object protection conforming to IP41*	9 1 5 9 0 0 4 3 5
Mounting Hardware		
	23" Rack-Mount Kit (2)*	9 1 5 9 0 1 9 0
	Surface Mount Kit for SEL-2730M and SEL-2730U*	9 1 5 9 0 0 5 5 0
Cable		
	8 ft AC Line Cord for 125/250V Power Supply*	9 1 5 9 0 0 3 7 7
	SEL-CA605 Ethernet Cable (RJ-45 M/RJ-45 M)*	Please see Online MOT or contact SEL REP or CSR for ordering information.
	SEL-C808 Fiber-Optic Cable (62.5/125 um, Multimode)*	Please see Online MOT or contact SEL REP or CSR for ordering information.
	SEL-C809 Singlemode Fiber-Optic Cable*	Please see Online MOT or contact SEL REP or CSR for ordering information.
	SEL-9330 125/250 Vdc or Vac w/o Conformal Coat (125/250 Vdc or Vac Input)*	9 3 3 0 A X X
	SEL-9330 125/250 Vdc or Vac with Conformal Coat (125/250 Vdc or Vac Input, Conformal Coat)*	9 3 3 0 A X 1
	SEL-9330 SEL-9330C Low-Voltage Power Supply (24/48 Vdc)*	9 3 3 0 C X X
	SEL-9330 SEL-9330C Low-Voltage Power Supply (Conformal Coated) (24/48 Vdc, Conformal Coat)*	9 3 3 0 C X 1
	SFP Transceiver for SEL-2730M (10/100/1000BASE-T Copper Ethernet)*	8 1 1 5 - 0 1
	SFP (1000BASE-SX, 850 nm, Multimode, LC Connector, 300 m for 62.5/125 micrometer Multimode Fiber and 500 m for 50/125 micrometer)*	8 1 3 1 - 0 1
	SFP (1000BASE-LX, 1310 nm, Single-Mode, LC Connector, 10 km)*	8 1 3 0 - 0 1
	SFP (1000BASE-LX, 1310 nm, Single-Mode, LC Connector, 20 km)*	8 1 3 0 - 0 2
	SFP (1000BASE-LX, 1310 nm, Single-Mode, LC Connector, 30 km)*	8 1 3 0 - 0 3
	SFP (1000BASE-LX, 1310 nm, Single-Mode, LC Connector, 40 km)*	8 1 3 0 - 0 4
	SFP (1000BASE-XD, 1550 nm, Single-Mode, LC Connector, 50 km)*	8 1 3 0 - 0 5

SFP (1000BASE-ZX, 1550 nm, Single-Mode, LC Connector, 80 km)*	8 1 3 0 - 0 6
SFP (1000BASE-ZX, 1550 nm, Single-Mode, LC Connector, 160 km)*	8 1 3 0 - 0 8
SFP (1000BASE-ZX, 1550 nm, Single-Mode, LC Connector, 200 km)*	8 1 3 0 - 1 0

* Additional Cost

⁽¹⁾ Multimode: 1300 nm, LC Connector, 2 km
Singlemode: 1310 nm, LC Connector, 15 km

⁽²⁾ Unit with mounting kit correctly installed for front-edge mounting will pass vibration test severity level Class 1.

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990