

## SEL-C276 EIA-232 Serial Cable with IRIG-B

Split cable for connecting an SEL communication processor to an SEL DTE device with a 9-pin female connector and a BNC IRIG-B input.<sup>(1)(2)</sup>

Part Number:

C 2 7 6 -

### Length<sup>(3)</sup>


Specify in Feet with Leading Zeros (Example: 5 Feet = 005) Max length 100 Feet

\* Additional Cost

<sup>(1)</sup> To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>.

<sup>(2)</sup> Indoor Use Only, CM-Rated

<sup>(3)</sup> The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the fiber-optic C276FZ/FD cable.



**CABLE:** 9 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket  
(Shielded: Alpha 1298C or equal)

SEL-2020/2030 (Data & IRIG)		SEL-2020/2030 (Data)	
RXD	2	ORANGE	3 TXD
TXD	3	RED	2 RXD
GND	5	YELLOW	5 GND
RTS	7	GREEN	8 CTS
CTS	8	WHITE	7 RTS
SHELL		SHIELD	NO CONNECTION
		IRIG-B Input	
+IRIG B	4	BLUE	CENTER
-IRIG B	6	BLACK	SHIELD

*Making Electric Power Safer, More Reliable, and More Economical®*

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990